




CASTOR, CAMBER and KING PIN INCLINATION HTM21



Year 2
study

Features

- Bench top unit simulating vehicle front steering arrangement
- Very visual unit
- Rolling road can be turned manually
- Variation of Castor, Camber, King Pin Inclination
- Accurate adjustment using protractors and flexible joints
- Many adjustments can be made to vary results

Description

Students often experience difficulty in understanding the principles of front wheel set-up on road vehicles, since the geometry involves angles in three dimensions.

The apparatus shows precisely how castor, camber and king pin inclination are set up and how centre point steering is achieved. A wheel and means of altering the

offset are included so that everything affecting centre point steering can be varied.

Vernier scales measure the castor angles and king pin inclination, while toe in and camber angles are measured from a longitudinal and vertical datum in the way in which they would be determined on a real vehicle. A hand driven rotating turntable simulates a rolling road, and may be turned at a slow enough speed to study wheel stability under running conditions.

Related laws

- Automotive
- King Pin inclination
- Toe in, toe out
- Geometry
- Castor angle
- Steering

- Vernier scale
- Cornering Forces

Learning capabilities

- To show how castor, camber and king pin inclination are set up
- To show how the steering linkage is related to toe-in
- To demonstrate the effect of wheel offset
- To observe the dynamic stability of the wheel under running conditions
- To measure the forces on the steering link
- To show how the weight of the car affects self centring

Technical Specification

- Ø250mm Running Wheel
- Ø380mm turntable
- ±5° Vernier Scale
- ±40° Protractor Scale

Recommended Ancillaries

- HTM21B

What's in the Box?

- 1 x HTM21 Assembly
- 1 x Combination spanner
- Hex Wrench
- Packing list
- Test sheet

Weights & Dimensions

- Weight: 10 kg
- Length: 500mm
- Width: 400mm
- Height: 370mm

Essential Services

- Sturdy Bench top

Operational Conditions

- Storage temperature: -10°C to +70°C
- Operating temperature range: +10°C to +50°C

- Operating relative humidity range: 0 to 95%, non condensing

Ordering information

To order this product, please call PA Hilton quoting the following code:
HTM21

All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure.

Copyright © 2018 P.A. Hilton Limited. All rights reserved. This technical leaflet, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of P. A. Hilton Limited. Hi-Tech Education is a registered trade mark of P. A. Hilton Limited.

COUNTRY OF ORIGIN - UK WARRANTY PERIOD - 2 YEARS